



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M16X250

Article number	07023.160.250
Brand	-
UBB	500647956803
UNSPSC	31161605
EAN	8717077283701
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	250 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ISO	4762
DIN	912
ASME	B18.3.1M
BS	4168-1
NF	E25-125
NEN	1241

Technical Specification

b	44
d-D	M16
dk (max.)	24
Full thread if $L \leq$	60
k (max.)	16
L (mm)	250
P	2
s	14

Technical Drawing

