



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M18X70

Article number	07023.180.070
Brand	-
UBB	500647957223
UNSPSC	31161605
EAN	8717077283749
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M18
Length	70 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ASME	B18.3.1M
DIN	912
NF	E25-125
NEN	1241
ISO	4762
BS	4168-1

Technical Specification

b	48
d-D	M18
dk (max.)	27
Full thread if $L \leq$	65
k (max.)	18
L (mm)	70
P	2.5
s	14

Technical Drawing

