



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M20X260

Article number	07023.200.260
Brand	-
UBB	500647960920
UNSPSC	31161605
EAN	8717077284111
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M20
Length	260 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-125
NEN	1241
DIN	912
ISO	4762
BS	4168-1
ASME	B18.3.1M

Technical Specification

b	52
d-D	M20
dk (max.)	30
Full thread if $L \leq$	75
k (max.)	20
L (mm)	260
P	2.5
s	17

Technical Drawing

