



Hexagon socket head cap screw ISO 4762 Steel Zinc plated 10.9 M10X35

Article number	07027.100.035
Brand	-
UBB	500650825911
UNSPSC	31162400
EAN	8717077297050
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	35 mm
Class	10.9
Driving features	Hexagon socket
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.3.1M
DIN	912
BS	4168-1
NEN	1241
NF	E25-125
ISO	4762

Technical Specification

b	32
d-D	M10
dk (max.)	16
Full thread if $L \leq$	40
k (max.)	10
L (mm)	35
s	8

Technical Drawing

