



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M10X155

Article number	07060.100.155
Brand	-
UBB	500645075564
UNSPSC	31161605
EAN	8717077057432
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	155 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	912
NEN	1241
BS	4168-1
ASME	B18.3.1M
NF	E25-125
ISO	4762

Technical Specification

b	32
d-D	M10
dk (max.)	16
Full thread if $L \leq$	40
k (max.)	10
L (mm)	155
P	1.5
s	8

Technical Drawing

