



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M10X230

Article number	07060.100.230
Brand	-
UBB	500645075986
UNSPSC	31161605
EAN	8717077057470
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	230 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

BS	4168-1
DIN	912
NF	E25-125
ASME	B18.3.1M
NEN	1241
ISO	4762

Technical Specification

b	32
d-D	M10
dk (max.)	16
Full thread if $L \leq$	40
k (max.)	10
L (mm)	230
P	1.5
s	8

Technical Drawing

