



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M14X270

Article number	07060.140.270
Brand	-
UBB	500644786591
UNSPSC	31161605
EAN	8717077027206
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M14
Length	270 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	912
ISO	4762
BS	4168-1
NF	E25-125
NEN	1241
ASME	B18.3.1M

Technical Specification

b	40
d-D	M14
dk (max.)	21
Full thread if $L \leq$	55
k (max.)	14
L (mm)	270
P	2
s	12

Technical Drawing

