



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M18X40

Article number	07060.180.040
Brand	-
UBB	950351415225
UNSPSC	31161605
EAN	8715492058478
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M18
Length	40 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	912
NF	E25-125
NEN	1241
ISO	4762
BS	4168-1
ASME	B18.3.1M

Technical Specification

b	48
d-D	M18
dk (max.)	27
Full thread if $L \leq$	65
k (max.)	18
L (mm)	40
P	2.5
s	14

Technical Drawing

