

Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M20X70



Article number	07060.200.070
Brand	-
UBB	950351417205
UNSPSC	31161605
EAN	8715492058775
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M20
Length (L) (mm)	70
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.3.1M
DIN	912
NF	E25-125
BS	4168-1
ISO	4762

Technical Specification

b	52
d_k (max.)	30
Full thread if $L \leq$	75
k (max.)	20
P	2.50
s	17

Technical Drawing

