



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M24X90

Article number	07060.240.090
Brand	-
UBB	950351420415
UNSPSC	31161605
EAN	8715492059390
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	90 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	912
BS	4168-1
NF	E25-125
ISO	4762
NEN	1241
ASME	B18.3.1M

Technical Specification

b	60
d-D	M24
dk (max.)	36
Full thread if $L \leq$	85
k (max.)	24
L (mm)	90
P	3
s	19

Technical Drawing

