

Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M27X40



Article number 07060.270.040

Brand -

UBB 500644799883

UNSPSC 31161605

EAN 8717077028531

PKG. of 10 Full Box Only

Technical Parameters

Diameter (d-D)	M27
Length (L) (mm)	40
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-125
ISO	4762
DIN	912
BS	4168-1
ASME	B18.3.1M

Technical Specification

b	66
d_k (max.)	40
Full thread if $L \leq$	90
k (max.)	27
P	3
s	19

Technical Drawing

