

## Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M27X75



Article number	07060.270.075
Brand	-
UBB	500644800368
UNSPSC	31161605
EAN	8717077028586
PKG. of 10	Full Box Only

### Technical Parameters

Diameter (d-D)	M27
Length (L) (mm)	75
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

### Standards

BS	4168-1
DIN	912
ISO	4762
ASME	B18.3.1M
NF	E25-125

### Technical Specification

b	66
$d_k$ (max.)	40
Full thread if $L \leq$	90
k (max.)	27
P	3
s	19

### Technical Drawing

