



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M27X200

Article number	07060.270.200
Brand	-
UBB	952351352663
UNSPSC	31161605
EAN	8715492059758
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M27
Length	200 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.3.1M
NEN	1241
BS	4168-1
NF	E25-125
DIN	912
ISO	4762

Technical Specification

b	66
d-D	M27
dk (max.)	40
Full thread if $L \leq$	90
k (max.)	27
L (mm)	200
P	3
s	19

Technical Drawing

