



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M30X140

Article number	07060.300.140
Brand	-
UBB	952351479318
UNSPSC	31161605
EAN	8715492059925
PKG. of 2	Full Box Only

Technical Parameters

Diameter	M30
Length	140 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4762
ASME	B18.3.1M
NF	E25-125
BS	4168-1
DIN	912
NEN	1241

Technical Specification

b	72
d-D	M30
dk (max.)	45
Full thread if $L \leq$	100
k (max.)	30
L (mm)	140
P	3.5
s	22

Technical Drawing

