



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M30X280

Article number	07060.300.280
Brand	-
UBB	952351354560
UNSPSC	31161605
EAN	8715492060044
PKG. of 2	Full Box Only

Technical Parameters

Diameter	M30
Length	280 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

BS	4168-1
DIN	912
NF	E25-125
NEN	1241
ISO	4762
ASME	B18.3.1M

Technical Specification

b	72
d-D	M30
dk (max.)	45
Full thread if $L \leq$	100
k (max.)	30
L (mm)	280
P	3.5
s	22

Technical Drawing

