



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 8.8 M3X20

Article number	07065.030.020
Brand	-
UBB	500577359259
UNSPSC	31161605
EAN	8715494328777
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	20 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread

Info
A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ISO	4762
NEN	1241
NF	E25-125
BS	4168-1
DIN	912
ASME	B18.3.1M

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if $L \leq$	20
k (max.)	3
L (mm)	20
P	0.5
s	2.5

Technical Drawing

