



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 8.8 M4X10

Article number	07065.040.010
Brand	-
UBB	500577359416
UNSPSC	31161605
EAN	8715494328791
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	10 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread

Info
A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	912
ISO	4762
NEN	1241
BS	4168-1
ASME	B18.3.1M
NF	E25-125

Technical Specification

b	20
d-D	M4
dk (max.)	7
Full thread if L ≤	25
k (max.)	4
L (mm)	10
P	0.7
s	3

Technical Drawing

