



Hexagon socket head cap screw with low head DIN 7984 Steel Plain 08.8 M6X22

Article number	07080.060.022
Brand	-
UBB	950351426370
UNSPSC	31161605
EAN	8715492061935
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	22 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Standards

DIN	7984
-----	------

Technical Specification

b (min.)	18
d-D	M6
dk	10
Full thread if $L \leq$	25
k	4
L (mm)	22
P	1
s	4

Technical Drawing

