



Hexagon socket head cap screw with low head DIN 7984 Steel Zinc plated 08.8 M6X70

Article number	07090.060.070
Brand	-
UBB	500645087940
UNSPSC	31161605
EAN	8717077058675
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	70 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070',

Standards

DIN	7984
-----	------

FABORY or with the steel
grade only, e.g. 'A2'.

Technical Specification

b (min.)	18
d-D	M6
dk	10
Full thread if $L \leq$	25
k	4
L (mm)	70
P	1
s	4

Technical Drawing

