



Hexagon socket head cap screw with low head DIN 7984 Steel Zinc plated 08.8 M8X40

| | |
|----------------|---------------|
| Article number | 07090.080.040 |
| Brand | - |
| UBB | 950351434606 |
| UNSPSC | 31161605 |
| EAN | 8715492063212 |
| PKG. of 200 | Full Box Only |

Technical Parameters

| | |
|-------------------|----------------------|
| Diameter | M8 |
| Length | 40 mm |
| Class | 08.8 |
| Driving features | Hexagon socket |
| Head shape | Low cylindrical head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc plated |
| Thread | Metric thread |

Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070',

Standards

| | |
|-----|------|
| DIN | 7984 |
|-----|------|

or with the steel
grade only, e.g. 'A2'.

FABORY

Technical Specification

| | |
|-------------------------|------|
| b (min.) | 22 |
| d-D | M8 |
| dk | 13 |
| Full thread if $L \leq$ | 30 |
| k | 5 |
| L (mm) | 40 |
| P | 1.25 |
| s | 5 |

Technical Drawing

