



**Hexagon socket head
shoulder screw UNC ASME
B18.3 Steel Plain 012.9
(#10)1/4X1.1/4**

Article number	07116.048.031
Brand	-
UBB	953351303656
UNSPSC	31161605
EAN	8715492066510
PKG. of 25	Full Box Only

Technical Parameters

Length	1.1/4 Inch
Class	012.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

Standards

BS	2470
ASME	B18.3

Info	Warning: electroplating of these products may cause hydrogen embrittlement.All dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for these screws is 3A,
------	--

plating can cause
thread fit problems.

FABURY

Technical Specification

A (max.)	0.375
D	0.25
D1	0.19
E	0.375
H (max.)	0.188
J	0.125
Threads per inch	24
D (min.)	0.246
D (max.)	0.248

Technical Drawing

