



Hexagon socket head shoulder screw tolerance h8 ISO ≈7379 Steel Plain 012.9 (M6)8X40

Article number 07117.060.040

Brand -

UBB 953351820519

UNSPSC 31161605

EAN 8715492067029

PKG. of 50 Full Box Only

Technical Parameters

Diameter (d-D) M6

d_s 8

Length (L) (mm) 40

Info Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Class 012.9

Driving features Hexagon socket

Head shape Cylindrical head

Material Steel

Thread direction Right

Standards

BS ≈4168-7

ISO ≈7379

ASME ≈B18.3.3M

Surface treatment	Plain
Thread	Metric thread

Info
SETTING THE STANDARD
 IN FASTENING SOLUTIONS

Warning:
 electroplating of
 these products may
 cause hydrogen
 embrittlement.

Technical Specification

b	11
d _k (max.)	13.27
d _s (nom.)	8
k (max.)	5.5
P	1
s	4
Tolerance h8 (max.)	8
Tolerance h8 (min.)	7.978

Technical Drawing

