



## Hexagon socket button head screw with flange ISO 7380-2 Steel Zinc plated 010.9 M3X25

Article number	07141.030.025
Brand	-
UBB	953351989413
UNSPSC	31161518
EAN	8715492067562
PKG. of 200	Full Box Only

### Technical Parameters

Diameter	M3
Length	25 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

#### Info

Warning: electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked

### Standards

ISO	7380-2
-----	--------

**FABORY** with a '0' preceding  
the property class  
mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

d-D	M3
dc (max.)	6.9
Full thread if $L \leq$	20
k (max.)	1.65
L (mm)	25
P	0.5
s	2

## Technical Drawing

