



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M3X18

Article number	07160.030.018
Brand	-
UBB	953351872098
UNSPSC	31161605
EAN	8715492070807
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	18 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	1241
NF	E25-125
ASME	B18.3.1M
ISO	4762
BS	4168-1
DIN	912

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if $L \leq$	20
k (max.)	3
L (mm)	18
P	0.5
s	2.5

Technical Drawing

