



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M4X25

Article number	07160.040.025
Brand	-
UBB	950351442039
UNSPSC	31161605
EAN	8715492070968
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	25 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	1241
NF	E25-125
DIN	912
BS	4168-1
ASME	B18.3.1M
ISO	4762

Technical Specification

b	20
d-D	M4
dk (max.)	7
Full thread if $L \leq$	25
k (max.)	4
L (mm)	25
P	0.7
s	3

Technical Drawing

