



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M8X20

Article number	07160.080.020
Brand	-
UBB	950351445917
UNSPSC	31161605
EAN	8715492071613
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	20 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.3.1M
ISO	4762
NEN	1241
DIN	912
NF	E25-125
BS	4168-1

Technical Specification

b	28
d-D	M8
dk (max.)	13
Full thread if L ≤	35
k (max.)	8
L (mm)	20
P	1.25
s	6

Technical Drawing

