



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M12X270

Article number	07160.120.270
Brand	-
UBB	500644821315
UNSPSC	31161605
EAN	8717077030688
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M12
Length	270 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	912
NF	E25-125
ISO	4762
NEN	1241
ASME	B18.3.1M
BS	4168-1

Technical Specification

b	36
d-D	M12
dk (max.)	18
Full thread if L ≤	50
k (max.)	12
L (mm)	270
P	1.75
s	10

Technical Drawing

