



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M14X20

Article number	07160.140.020
Brand	-
UBB	500645103374
UNSPSC	31161605
EAN	8717077060210
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M14
Length	20 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.3.1M
NF	E25-125
ISO	4762
BS	4168-1
DIN	912
NEN	1241

Technical Specification

b	40
d-D	M14
dk (max.)	21
Full thread if L ≤	55
k (max.)	14
L (mm)	20
P	2
s	12

Technical Drawing

