



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M14X25

Article number	07160.140.025
Brand	-
UBB	500645103457
UNSPSC	31161605
EAN	8717077060227
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M14
Length	25 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	4168-1
NF	E25-125
ISO	4762
ASME	B18.3.1M
DIN	912
NEN	1241

Technical Specification

b	40
d-D	M14
dk (max.)	21
Full thread if $L \leq$	55
k (max.)	14
L (mm)	25
P	2
s	12

Technical Drawing

