



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M14X75

Article number	07160.140.075
Brand	-
UBB	500645103523
UNSPSC	31161605
EAN	8717077060234
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	75 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4762
DIN	912
NEN	1241
BS	4168-1
ASME	B18.3.1M
NF	E25-125

Technical Specification

b	40
d-D	M14
dk (max.)	21
Full thread if $L \leq$	55
k (max.)	14
L (mm)	75
P	2
s	12

Technical Drawing

