



Hexalobular socket head cap screw ISO 14579 Steel Zinc plated 8.8 M8X35

Article number	07165.080.035
Brand	-
UBB	500645104513
UNSPSC	31161605
EAN	8717077060333
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	35 mm
Class	8.8
Driving features	Hexalobular
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	14579
-----	-------

Technical Specification

b	28
d-D	M8
dk (max.)	13
Full thread if $L \leq$	35
k (max.)	8
L (mm)	35
P	1.25
Socket	45

Technical Drawing

