



Hexagon socket head cap screw DIN 912 Steel Zinc plated yellow passivated 8.8 M3X16

Article number	07170.030.016
Brand	-
UBB	500645104851
UNSPSC	31161605
EAN	8717077060364
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	16 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	E25-125
DIN	912
BS	4168-1
NEN	1241
ASME	B18.3.1M
ISO	4762

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if L ≤	20
k (max.)	3
L (mm)	16
P	0.5
s	2.5

Technical Drawing

