



**Hexagon socket head cap
screw UNC 1936 series
ASME B18.3 Alloy steel
ASTM A574 Plain 5/16X2.3/4**

Article number	07210.079.069
Brand	-
UBB	951351505304
UNSPSC	31161605
EAN	8715492077974
PKG. of 100	Full Box Only

Technical Parameters

Diameter	5/16 Inch
Length	2.3/4 Inch
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Alloy steel
Material technical	ASTM A574
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

Info

Marking in accordance with ASTM A574 with manufacturer's identification mark only. Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems. Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ASME	B18.3
------	-------

Technical Specification

A	0.4375
H	0.3125
J	0.21875
LT (min.)	1.125
Threads per inch	18

Technical Drawing

