



Hexagon socket countersunk head screw ISO 10642 Steel Plain 08.8 M3X6

Article number 07465.030.006

Brand -

UBB 500649271276

UNSPSC 31161518

EAN 8717077196957

PKG. of 100 Full Box Only

Technical Parameters

Diameter	M3
Length	6 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class

Standards

DIN	≈7991
ISO	10642

FABORY mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technical Specification

b (min.)	18
d-D	M3
dk (max.)	5.81
Full thread if $L \leq$	25
k (max.)	1.86
L (mm)	6
P	0.5
s	2
α	90

Technical Drawing

