



## Hexagon socket countersunk head screw ISO 10642 Steel Plain 08.8 M3X18

Article number	07465.030.018
Brand	-
UBB	500649271763
UNSPSC	31161518
EAN	8717077197008
PKG. of 500	Full Box Only

### Technical Parameters

Diameter	M3
Length	18 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

#### Info

All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class

### Standards

ISO	10642
DIN	≈7991

**FABORY** mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

b (min.)	18
d-D	M3
dk (max.)	5.81
Full thread if $L \leq$	25
k (max.)	1.86
L (mm)	18
P	0.5
s	2
$\alpha$	90

## Technical Drawing

