



Carriage bolt DIN 603 Steel Plain 8.8 M6X40

Article number	08310.060.040
Brand	-
UBB	950351617366
UNSPSC	31161612
EAN	8715492558268
PKG. of 200	Full Box Only

Technical Parameters

Threaded pitch (P)	1
Diameter (d-D)	M6
Length (L) (mm)	40
Class	8.8
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	≈8677
BS	≈4933
DIN	603

Technical Specification

b (min.): 125mm<L≤200mm	24
b (min.): L≤125mm	18
d _k (max.)	16.55
k (max.)	3.88
P	1
f _n (max.)	4.6
V _n (max.)	6.48

Technical Drawing

