



**Assembly set for pressure vessels ISO 4014/4032 Steel Hot dip galvanized 5.6/5.2 M12X50**

Article number	08753.120.050
Brand	-
UBB	500650920613
UNSPSC	31161620
EAN	8717077306530
PKG. of 100	Full Box Only

**Technical Parameters**

Diameter	M12
Length	50 mm
Class	5.6/5.2
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10°C up to +300°C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a

**Standards**

ISO	4014/4032
-----	-----------

# FABORY

certificate EN 10204  
3.1 by marking  
the fasteners  
with the property  
class and the  
manufacturer's mark.  
This recognition is  
equally accepted  
by Lloyd's Register  
Energy.

## Technical Specification

b (min.): 125mm $L \leq 200$ mm	36
b (min.): $L > 200$ mm	49
b (min.): $L \leq 125$ mm	30
d-D	M12
k	7.5
L (mm)	50
m (max.)	10.8
P	1.75
s	18

## Technical Drawing

