



## Assembly set for pressure vessels ISO 4014/4032 Steel Hot dip galvanized 5.6/5.2 M12X60

Article number	08753.120.060
Brand	-
UBB	500650920878
UNSPSC	31161620
EAN	8717077306554
PKG. of 100	Full Box Only

### Technical Parameters

Diameter (d-D) M12

Length (L) (mm) 60

#### Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10°C up to +300°C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13 Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a certificate EN 10204 3.1 by marking the fasteners with the property class and the manufacturer's mark. This recognition is equally accepted

### Standards

ISO 4014/4032

by Lloyd's Register  
Energy.

**FABUKY**  
Class **OF COURSE** 6/5.2  
SETTING THE STANDARD

Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

### Technical Specification

b (min.): 125mm <math>L \leq 200\text{mm}</math>	36
b (min.): $L > 200\text{mm}$	49
b (min.): $L \leq 125\text{mm}$	30
k	7.5
m (max.)	10.8
P	1.75
s	18

### Technical Drawing

