



## Assembly set for pressure vessels ISO 4014/4032 Steel Hot dip galvanized 5.6/5.2 M16X75

Article number	08753.160.075
Brand	-
UBB	500650921454
UNSPSC	31161620
EAN	8717077306615
PKG. of 25	Full Box Only

### Technical Parameters

Diameter (d-D)	M16
Length (L) (mm)	75

### Standards

ISO	4014/4032
-----	-----------

#### Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from  $-10^{\circ}\text{C}$  up to  $+300^{\circ}\text{C}$ . Meets the requirements of AD2000-W7, TRD106 and DIN 267-13 Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a certificate EN 10204 3.1 by marking the fasteners with the property class and the manufacturer's mark. This recognition is equally accepted

by Lloyd's Register  
Energy.

**FABUKY**  
Class **OF COURSE** 6/5.2  
SETTING THE STANDARD

Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

### Technical Specification

b (min.): 125mm <math>L \leq 200\text{mm}</math>	44
b (min.): $L > 200\text{mm}$	57
b (min.): $L \leq 125\text{mm}$	38
k	10
m (max.)	14.8
P	2
s	24

### Technical Drawing

