

Swiss Tech Slot drill 3 flute DIN 844 Long Cobalt HSS Uncoated 12,0MM



Article number	0Q403458
Brand	-
UBB	500649980942
UNSPSC	27110000
EAN	5036140202726
PKG. of 1	Full Box Only

Technical Parameters

Flute length	53
Number of flutes	3
Shank diameter tolerance	h6
Coolant delivery	External
Basic material	Cobalt HSS
Material grade	M42
Cutter diameter	12
Plunge type	Centre cutting
Reach type	Standard Neck
Length type	Long
Milling application	Slotting, Profiling, Semi-finishing, Finishing
Material application	Carbon Steel, Alloy Steel, Copper, Aluminium
Helix direction	Right
Cutter diameter tolerance	e8
Number of cutting ends	1
End mill type	Slot Drill
Coating	Uncoated
Cutting direction	Right
Flute type	Helical

Standards

DIN 844, 1835B

Helix angle	30
Total length (mm)	110
Shank size (mm)	12
Shank type	Weldon Flat

STANDARD
IN FASTENING SOLUTIONS

UP COURSE