



RODA 3/8" RATCHET

Article number	1014300A
Brand	-
UBB	500617267041
UNSPSC	27112713
EAN	8717659222616
PKG. of 1	Full Box Only

Technical Parameters

Width	29
Height	37
Length	130
Max. operation pressure	6.3
Tool insertion	3/8 inch
Idle rotational speed	260
Air inlet device-sided	R 1/4 inch
Max. loosening torque	34
Max. tightening torque	34
Ratcheting model	Yes
Impulse driver	Yes
Air volume required	108

Standards