

Hexagon nut turned DIN 934 Steel Plain [6] turned M2

Article number	11000.020.001
Brand	-
UBB	950355536687
UNSPSC	31161727
EAN	8715492567130
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2
Class	[6]
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	turned

Standards

DIN	934
NF	E25-401
NEN	1560

Technical Specification

d-D	M2
m	1.6
P	0.4
s	4

Technical Drawing

