

Hexagon nut turned DIN 934 Steel Plain [6] turned M3

Article number	11000.030.001
Brand	-
UBB	950355063930
UNSPSC	31161727
EAN	8715492567178
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M3
Class	[6]
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	turned

Standards

DIN	934
NF	E25-401
NEN	1560

Technical Specification

d-D	M3
m	2.4
P	0.5
s	5.5

Technical Drawing

