

Hexagon nut left hand thread DIN 934 Steel Zinc plated |8| M10 (LH)

Article number	11042.100.001
Brand	-
UBB	950355777331
UNSPSC	31161727
EAN	8715492568175
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Left (LH)
Surface treatment	Zinc plated
Thread	Metric thread
Info	left hand thread

Standards

NF	E25-401
NEN	1560
DIN	934

Technical Specification

d-D	M10
m	8
P	1.5
s	17

Technical Drawing

