

Hexagon nut left hand thread DIN 934 Steel Zinc plated |8| M24 (LH)

Article number	11042.240.001
Brand	-
UBB	500621759504
UNSPSC	31161727
EAN	8715494508223
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M24
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Left (LH)
Surface treatment	Zinc plated
Thread	Metric thread
Info	left hand thread

Standards

NEN	1560
NF	E25-401
DIN	934

Technical Specification

d-D	M24
m	19
P	3
s	36

Technical Drawing

