



**Hexagon connection nut
H=3xD oversized thread
Steel Hot dip galvanized M10**

Article number	11411.100.001
Brand	-
UBB	500621922375
UNSPSC	31161727
EAN	8715494514286
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info	Oversized hot dip galvanized nuts are manufactured with thread tolerance class 6AZ and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6g before coating.As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced disadvantageously as the thread will be protected by the zinc
------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Standards

layer of the mating
part.oversized

FABORY

Technical Specification

d-D	M10
m	30
P	1.5
s	17

Technical Drawing

