



Hexagon nut with flange DIN 6923 Steel Zinc plated yellow passivated 8 M10

Article number	11595.100.001
Brand	-
UBB	950355783842
UNSPSC	31161727
EAN	8715492573704
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Info

Specific features of hexagon nuts with flange: The flange enables built up forces under the nut to be spread over a larger area, consequently resulting in lower surface pressure. Large (oversized) holes and/or tooling holes can be covered by the flange. Washers are not necessary.

Standards

NF	E25-406
DIN	6923
ISO	4161

Technical Specification

d-D	M10
-----	-----

Technical Drawing

dc (max.) 21.8

m (max.) 10

P 1.5

s 15

