



Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated [5] M3

Article number	12300.030.001
Brand	-
UBB	950355115599
UNSPSC	31161727
EAN	8715492576804
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M3
Class	[5]
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈10511
NF	E25-412
DIN	985

Technical Specification

d-D	M3
h	4
P	0.5
s	5.5

Technical Drawing

