



Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated [5] M12

Article number	12300.120.001
Brand	-
UBB	950355116258
UNSPSC	31161727
EAN	8715492576880
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Class	[5]
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈10511
DIN	985
NF	E25-412

Technical Specification

d-D	M12
h	12
P	1.75
s	19

Technical Drawing

