



Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated |5| M14

Article number	12300.140.001
Brand	-
UBB	950355116332
UNSPSC	31161727
EAN	8715492576897
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M14
Class	5
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈10511
NF	E25-412
DIN	985

Technical Specification

h	14
P	2
s	22

Technical Drawing

